

ZI Haneboesch L-4562 Differdange I UXFMBOURG Phone: +352 58 22 82 1 Fax: +352 58 49 35 E-mail: sales@airtech.lu Website: www.airtech.lu

### **Data Sheet**

# **DAHLAR® RELEASE BAG 460**

## High temperature self releasing tubular bagging film

#### DESCRIPTION

Dahlar® Release Bag 460 is a self releasing multi-layer bagging film for direct contact with prepreg for fabrication of hollow parts. It exhibits superior strength, temperature resistance and vacuum integrity of Airtech's multi-layer film technology. Dahlar® Release Bag 460 exhibits excellent release of epoxy and polyester resins.

This product is also available in gusseted tubing (GT). Thanks to the gusset folding, Dahlar® Release Bag 460 is easier to position accurately in hollow parts. Upon application of pressure the bag will easily expand to fit to the shape of the part which is very useful in applications where there are variations in the part diameter. This development ensures even application of internal pressure in cases of small diameter parts, where the insertion of a standard lay flat tube bagging film can be problematic.

#### BENEFITS

- Multi-layer construction combines release and vacuum performance in a single material.
- Easier to position accurately in hollow section, reduces cycle time, and improves quality.
- Easier to remove after cure reducing cycle time.

#### TECHNICAL DATA

Test method

Material type PMP, Nylon, multi-layer

Elongation at break 425 % ASTM D 882 Tensile strength 60 MPa ASTM D 882

Maximum use temperature 190°C

Materials to avoid Compatible with most resin systems

Colour Clear opaque

Shelf life Unlimited when stored in original packaging at 22°C

#### SIZES

Thickness	Width	Forms Available <sup>*</sup>
70 μm (0,0027 inch)	up to 0,304 m (12 inches)	LFT, GT

- For more sizes, see the Commonly Used Sizes chart in this section.
- Custom shapes and sizes are available, please contact Airtech for more information.



\*SHT=Sheeting



CF=Centerfold



LFT=Lay-Flat Tubing



GT=Gusseted Tubing



G=Gusseted

#### NOTES

• The maximum use temperature is dependent upon the duration at maximum temperature and is process specific, Airtech recommends testing prior to use.

Last updated: 2015-11-04

Catalogue position: Bagging films