

# 832HDA



## General Purpose Epoxy

832HDA is a 2-part, low-viscosity, black, general-purpose epoxy potting compound. The epoxy cures to a rigid finish, making it suitable for protecting circuits from physical impacts such as shocks and vibrations. The low mixed viscosity enables superior wetting that ensures complete encapsulation for even the most complicated circuit geometries.

832HDA protects against harsh environmental exposure such as humidity, salt water, fungus, corrosive gases and many harsh chemicals. The epoxy is also electrically insulating and protects circuits from static discharge and arcing.



## Features & Benefits

- Convenient 1:1 mix ratio
- Low mixed viscosity of 2 100 cP
- Adheres to many substrates, including plastic, ceramics, metals and glass
- Excellent electrical insulating properties
- Resistant to humidity and water (allows for submersion when needed)
- Solvent-free

## Available Packaging

| Cat. No.     | Packaging      | Net Vol. | Net Wt. |
|--------------|----------------|----------|---------|
| 832HDA-25ML  | Dual syringe   | 25 mL    | 26.7 g  |
| 832HDA-50ML  | Dual cartridge | 46 mL    | 49.1 g  |
| 832HDA-400ML | Dual cartridge | 380 mL   | 406 g   |
| 832HDA-7.4L  | 2 Pail kit     | 7.4 L    | 7.91 kg |
| 832HDA-40L   | 2 Pail kit     | 40 L     | 42.7 kg |

## Contact Information

MG Chemicals, 1210 Corporate Drive  
Burlington, Ontario, Canada L7L 5R6

Email: [support@mgchemicals.com](mailto:support@mgchemicals.com)

Phone: North America: +(1)800-340-0772

International: +(1) 905-331-1396

Europe: +(44)1663 362888

## Cured Properties

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Resistivity                            | $1.3 \times 10^{13} \Omega \cdot \text{cm}$ |
| Breakdown Voltage @ 2.8 mm             | 47 800 V                                    |
| Dielectric Strength @ 2.8 mm           | 408 V/mil                                   |
| Hardness                               | 81 D                                        |
| Tensile Strength                       | 39 N/mm <sup>2</sup>                        |
| Compressive Strength                   | 105 N/mm <sup>2</sup>                       |
| Lap Shear (stainless steel)            | 6.9 N/mm <sup>2</sup>                       |
| (aluminum)                             | 7.4 N/mm <sup>2</sup>                       |
| Glass Transition Temperature ( $T_g$ ) | 53 °C                                       |
| CTE Prior $T_g$                        | 56 ppm/°C                                   |
| CTE After $T_g$                        | 222 ppm/°C                                  |
| Thermal Conductivity @ 25 °C           | 0.2 W/(m·K)                                 |
| Service Temperature Range              | -50–140 °C                                  |
| Intermittent Temperature               | 200 °C                                      |

## Usage Parameters

|                     |        |
|---------------------|--------|
| Working Time        | 45 min |
| Mix Ratio by Volume | 1:1    |
| Mix Ratio by Weight | 1.22:1 |

## Uncured Properties

|                       |          |
|-----------------------|----------|
| Mixed Density         | 1.1 g/mL |
| Density (A)           | 1.2 g/mL |
| (B)                   | 1.0 g/mL |
| Viscosity @ 25 °C (A) | 3.2 Pa·s |
| (B)                   | 1.3 Pa·s |

## Application Instructions

Read the product SDS and Application Guide for more detailed instructions before using this product (downloadable at [www.mgchemicals.com](http://www.mgchemicals.com)).

## Recommended Preparation

Clean the substrate with Isopropyl Alcohol, MG #824, so the surface is free of oils, dust, and other residues.


## Mixing

1. Scrape settled material free from the bottom and sides of the part A container; stir the contents until homogenous. Use a paint shaker if available.
2. Measure 1 part by volume of the part A and pour into the mixing container. Ensure all contents are transferred by scraping the container.
3. Measure 1 part by volume of the part B and pour into the mixing container. Ensure all contents are transferred by scraping the container.
4. Thoroughly and gently mix parts A and B together. Avoid introducing air bubbles.
5. To de-air, let sit for 15 minutes or put in a vacuum chamber at 25 inHg for 2 minutes.
6. If bubbles are present at the top, break them gently with the mixing paddle.
7. Pour the mixture into a container holding the components to be protected.
8. Close the part A and B containers tightly between uses to prevent skinning.

## Syringe or Cartridge

1. Twist and remove the cap from the syringe or cartridge. Do not discard cap.
2. Dispense a small amount to ensure even flow of both parts.
3. (Optional) Attach a static mixer.
  - a. Dispense and discard 5 to 10 mL of the product to ensure a homogeneous mixture.
  - b. After use, dispose of static mixer.
4. Without a static mixer, dispense material on a mixing surface or container, and thoroughly mix parts A and B together.
5. To stop the flow, pull back on the plunger.
6. Clean nozzle to prevent contamination and material buildup.
7. Replace the cap on the syringe or cartridge.

## Viscosity vs. Temperature



If crystallization/solidification occurs, reconstitute the product by warming to between 55 and 65 °C. Let the material cool to room temperature before mixing, to prevent flash cure.

Mixing >500 g at a time decreases working time and can lead to a flash cure. Limit the size of hand-mixed batches. For large production volumes, contact MG Chemicals Technical Support for assistance.

## Dispensing Accessories

Consult the table below for accessory selection. See the Dispensing Accessories Application Guide for usage instructions.

| Cat. No.     | Dispensing Gun | Static Mixer |
|--------------|----------------|--------------|
| 832HDA-25ML  | N/A            | 8MT-25       |
| 832HDA-50ML  | 8DG-50-1-1     | 8MT-50       |
| 832HDA-400ML | 8DG-400-1-1    | 8MT-450      |

## Cure Instructions

Allow to cure at room temperature for 24 hours, or cure in an oven at one of these time/temperature options:

| Temperature | 65 °C | 80 °C  | 100 °C |
|-------------|-------|--------|--------|
| Time        | 1 h   | 45 min | 15 min |

## Storage and Handling

Store between 16 and 27 °C in a dry area, away from sunlight (see SDS).

## Disclaimer

This information is believed to be accurate. It is intended for professional end-users who have the skills required to evaluate and use the data properly. M.G. Chemicals Ltd. does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.