



Technical Data Sheet

SILASTIC™ RTV-3110 Mold-Making Base **SILASTIC™ RTV-3112 Mold-Making Base** **SILASTIC™ RTV-3120 Mold-Making Base**

General purpose silicone moldmaking rubbers.

Features & Benefits

- Two-part RTV silicone rubbers
- Low mixed viscosity
- Adjustable cure times
- Easy to use
- Reproduce intricate details
- Works in a wide range of service temperatures

Composition

- Condensation cure silicone RTV rubbers

Applications

- Recommended for simple patterns with no undercuts
- SILASTIC™ RTV-3110 Mold-Making Base can be used where vacuum de-airing isn't always required
- Can be used in electronic potting and encapsulating applications

Typical Properties

Specification Writers: These values are not intended for use in preparing specifications.

Test	Property	Unit	SILASTIC™ RTV-3110 Mold-Making Base ¹	SILASTIC™ RTV-3112 Mold-Making Base ¹	SILASTIC™ RTV- 3120 Mold-Making Base ¹
As supplied					
	Color		White	White	Red
	Viscosity at 25°C (77°F)	poise	130	280	280
	Specific gravity at 25°C (77°F)		1.14	1.30	1.45
Physical and mechanical properties, as cured					
	Useful temperature range	°C (°F)	-55 to 200 (-67 to 392)	-55 to 250 (-67 to 482)	-55 to 300 (-67 to 572)
	Tensile strength, die C	psi	395	640	582
	Elongation	percent	170	127	128
	Durometer hardness, Shore A	points	45	58	56

1. Results were obtained using SILASTIC™ RTV-3010-S Catalyst at 10:1 base to catalyst ratio. Wide departures from normal 10:1 ratio may slightly alter physical properties such as hardness and elongation. Based on sample thickness of 125 mils, cured 24 hours at room temperature.

Typical Properties (Cont.)

Test	Property	Unit	SILASTIC™ RTV-3110 Mold-Making Base	SILASTIC™ RTV-3112 Mold-Making Base	SILASTIC™ RTV-3120 Mold-Making Base
Electrical properties, as cured					
ASTM ² D 150	Dielectric constant at 25°C (77°F)		3.26	3.56	3.72
	100 Hz		3.16	3.32	3.7
	100 kHz				
ASTM D 150	Dissipation factor at 25°C (77°F)		0.0056	0.0135	0.0103
	100 Hz		0.0022	0.0038	0.003
	100 kHz				
ASTM D 149	Dielectric strength	volts/mil	456	470	418
ASTM D 257	Volume resistivity	ohm-cm	5.68 E+14	2.72 E+14	3.46 E+14

Catalyst	Color	Consistency	Demold Time ³	Cure Conditions
DOWSIL™ 4 Catalyst (Fast rate, 200:1 ratio, no corrosion inhibitor)	Clear straw	Liquid	10 minutes–2 ½ hours	Room temperature - any thickness or in confined places
SILASTIC™ RTV-3000 F Catalyst (Fast rate, 20:1 ratio, corrosion inhibitor)	Light tan	Paste	25 minutes–2 hours	Room temperature - any thickness or in confined spaces
SILASTIC™ RTV-3010-S Catalyst (10:1 ratio, corrosion inhibitor)	Light blue	Paste	7–12 hours	Room temperature - any thickness or in confined spaces

2. ASTM: American Society for Testing and Materials

3. Demold time varies based on the Dow RTV base used with the catalyst

Description

SILASTIC™ RTV-3100 Series are pourable rubber bases that become firm, flexible silicone rubber when cured. There is a choice of three catalysts to select from in order to tailor your working times and cure rates. SILASTIC™ RTV-3100 Series:

- Is easily mixed and poured
- Cures at room temperature in any thickness
- Gives accurate reproduction of masters for moldmaking
- Provides a wide service temperature range

Catalysts

A common catalyst concentration is 10:1 base to catalyst by weight, which assures more accurate measuring and mixing of catalyst. Varying the catalyst concentration will change the curing rate as indicated on Table 1. Decreasing the catalyst level will slow the cure and give longer working and demold times. Keep all catalyst containers tightly closed when not in use.

Note: A 10:1 mixing ratio is not recommended for DOWSIL™ 4 Catalyst or SILASTIC™ RTV-3000 F Catalyst. Do not use SILASTIC™ RTV-3010-S Catalyst or SILASTIC™ RTV-3000 F Catalyst when molding polyesters because the polyester can be inhibited. DOWSIL™ 4 Catalyst is recommended for polyester molds.

Table 1: Base/Catalyst Ratios, Working Times and Demold Times

	Base/Catalyst Mixing Ratio by Weight	Approximate Working Time	Approximate Demold Time
SILASTIC™ RTV-3110 Base			
SILASTIC™ RTV-3010-S Catalyst	5:1	1 hour	5 hours
	10:1	2 hours	7 hours
	20:1	3 hours	12 hours
SILASTIC™ RTV-3000 F Catalyst	10:1	10 minutes	27 minutes
	20:1	40 minutes	80 minutes
DOWSIL™ 4 Catalyst	100:1	3 minutes	10 minutes
	200:1	5 minutes	20 minutes
	400:1	20 minutes	2 hours
SILASTIC™ RTV-3112 Base			
SILASTIC™ RTV-3010-S Catalyst	5:1	30 minutes	6 hours
	10:1	1 hour	8 hours
	20:1	2 hours	12 hours
SILASTIC™ RTV-3000 F Catalyst	10:1	12 minutes	37 minutes
	20:1	28 minutes	100 minutes
DOWSIL™ 4 Catalyst	100:1	2 minutes	10 minutes
	200:1	5 minutes	20 minutes
	400:1	15 minutes	1½ hours
SILASTIC™ RTV-3120 Base			
SILASTIC™ RTV-3010-S Catalyst	5:1	30 minutes	6 hours
	10:1	1 hour	8 hours
	20:1	2 hours	12 hours
SILASTIC™ RTV-3000 F Catalyst	10:1	8 minutes	25 minutes
	20:1	25 minutes	1½ hours
DOWSIL™ 4 Catalyst	100:1	2 minutes	10 minutes
	200:1	5 minutes	30 minutes
	400:1	15 minutes	2½ hours

How to Use

Substrate Penetration

The surface of the original should be clean and free of loose material. If necessary, and in particular with porous substrates, use a suitable release agent such as petroleum jelly or soap solution.

Mixing

Thoroughly stir SILASTIC™ RTV-3100 Series bases before using, as filler separation may occur upon prolonged standing. Weigh the base and appropriate catalyst into a clean container, mix together until the catalyst is completely dispersed in the base. Hand or mechanical mixing can be used, but do not mix for an extended period of time or allow the temperature to exceed 35°C (95°F).

How to Use (Cont.)

Mixing (Cont.)

With the exception of SILASTIC™ RTV-3110 Base, it is strongly recommended that entrapped air be removed in a vacuum chamber, allowing the mix to completely expand and then collapse. A vacuum of at least 28 inches of mercury should be held until most bubbling has ceased. After an additional 1–2 minutes under vacuum, the mix should be inspected and if free of air bubbles, can then be used. A volume increase of 3–5 times will occur on vacuum de-airing the mixtures, so a suitably large container should be chosen.

Caution: Prolonged vacuum will remove volatile components from the mix and may result in poor thick section and non-typical properties.

Air entrapment can be minimized by mixing a small quantity of base and catalyst, then using a brush, painting the original with a thin layer. Leave at room temperature until the surface is bubble free and the layer has begun to cure. Mix a further quantity of base and catalyst and proceed as follows to produce a final mold.

Pouring the Mixture and Curing

Pour the mixed base and catalyst as soon as possible onto the original, avoiding air entrapment. The catalyzed material will cure to a flexible rubber and the mold can then be removed (see table of Typical Properties for details). If the working temperature is significantly lower than 23°C (73.4°F), the cure time will be longer. If the room temperature or humidity is very high, the working time of the catalyzed mixture will be reduced. The final mechanical properties will be reached within 7 days.

Deep-section Cure

SILASTIC™ RTV-3100 Series may depolymerize when overheated in total confinement. To minimize this effect, electrical pottings which must operate in total confinement at elevated temperatures must be given a graduated post cure which allows volatiles to escape. During the graduated post cure, the temperature should be increased approximately 25°C (77°F) per hour depending upon thickness of the potted section. A final bake of two to four hours at a temperature 50°C (122°F) degrees above the maximum operating temperature of the device is recommended.

Use at High Temperatures

Some molds produced from condensation cure silicone rubbers can degrade when exposed to temperatures above 150°C (302°F) over a period of time or when totally confined in storage at high ambient temperatures. This can result in softening and loss of elastic properties.

Electronic Applications

SILASTIC™ RTV-3100 Series can be used in electronic applications using the SILASTIC™ RTV-3010-S Catalyst or SILASTIC™ RTV-3000 F Catalyst. The cured rubbers exhibit good dielectric properties.

In potting with SILASTIC™ RTV-3100 Series, the part or assembly to be packaged is placed in a form with clearance at all points when sealing is necessary. This form may be made of paper, aluminum foil, metal or plastic.

A release agent may be used to aid in demolding.

When printed circuit boards and similar assemblies are to be dip coated, select the viscosity grade that will give the desired coating thickness.

How to Use (Cont.)**Electronic Applications (Cont.)**

To apply SILASTIC™ RTV-3100 Series as a conformal coating, immerse parts in the catalyzed compound, withdraw them slowly, pausing just before the part leaves the dip tank to minimize stringing and hang on a rack to cure. Allow one to two hours between dips. Two dips in a low viscosity grade encapsulant are suggested for optimum protection.

For maximum assurance of void-free potting, pour the silicone RTV rubber, then apply a vacuum to facilitate the removal of air.

**Handling
Precautions**

PRODUCT SAFETY INFORMATION REQUIRED FOR SAFE USE IS NOT INCLUDED IN THIS DOCUMENT. BEFORE HANDLING, READ PRODUCT AND SAFETY DATA SHEETS AND CONTAINER LABELS FOR SAFE USE, PHYSICAL AND HEALTH HAZARD INFORMATION. THE SAFETY DATA SHEET IS AVAILABLE ON THE DOW WEBSITE AT DOW.COM, OR FROM YOUR DOW SALES APPLICATION ENGINEER, OR DISTRIBUTOR, OR BY CALLING DOW CUSTOMER SERVICE.

**Usable Life and
Storage**

Product should be stored at or below 32°C (89.6°F) in original, unopened containers.

Limitations

This product is neither tested nor represented as suitable for medical or pharmaceutical uses.

Not intended for human injection. Not intended for food use.

**Health and
Environmental
Information**

To support customers in their product safety needs, Dow has an extensive Product Stewardship organization and a team of product safety and regulatory compliance specialists available in each area.

For further information, please see our website, dow.com or consult your local Dow representative.

**Disposal
Considerations**

Dispose in accordance with all local, state (provincial) and federal regulations. Empty containers may contain hazardous residues. This material and its container must be disposed in a safe and legal manner.

It is the user's responsibility to verify that treatment and disposal procedures comply with local, state (provincial) and federal regulations. Contact your Dow Technical Representative for more information.

**Product
Stewardship**

Dow has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our product stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our product stewardship program rests with each and every individual involved with Dow products - from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

Customer Notice

Dow strongly encourages its customers to review both their manufacturing processes and their applications of Dow products from the standpoint of human health and environmental quality to ensure that Dow products are not used in ways for which they are not intended or tested. Dow personnel are available to answer your questions and to provide reasonable technical support. Dow product literature, including safety data sheets, should be consulted prior to use of Dow products. Current safety data sheets are available from Dow.

dow.com

NOTICE: No freedom from infringement of any patent owned by Dow or others is to be inferred. Because use conditions and applicable laws may differ from one location to another and may change with time, Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where Dow is represented. The claims made may not have been approved for use in all countries. Dow assumes no obligation or liability for the information in this document. References to "Dow" or the "Company" mean the Dow legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED.



©™ Trademark of The Dow Chemical Company ("Dow") or an affiliated company of Dow
SILASTIC™ RTV-3110 Mold-Making Base, SILASTIC™ RTV-3112 Mold-Making Base,
SILASTIC™ RTV-3120 Mold-Making Base
© 2017–2025 The Dow Chemical Company. All rights reserved.